





Ducted Applications up to 3,000 CFM

The most efficient wet dust collectors on the market, the Uni-Wash series of wet dust collectors are capable of collecting dust down to 3 micron in size consuming only 3" wg. static pressure

Wet type dust collection is required for the safe collection of combustible metal dust. Wet Type Dust Collection has also been used effectively in many other difficult applications in place of cartridge collectors. ProVent's unique scrub design has been an industry standard for over 40 years and continues to lead the industry in Wet Type dust Collection efficiency.

Standard Features

Integral High Efficiency Fan Assemblies

- Injection Molded GRP Polyamide, Backward Curved Airfoil, Spark Resistant, Corrosionproof.

304 Stainless Steel Scrub Components

- Superior construction where it is needed the

2-Part Epoxy Internal Tank Coating

- AmerLock-2 by Ameron provides exceptional corrosion protection in harsh industrial and marine corrosive environments.

Urethane Mastic External Coating

- Durethane DTM by PPG chemically resistant and extremely durable. Provides excellent corrosion resistance with superior color and gloss retention.

95% Efficient consuming only 3" wg

- The most efficient wet dust collector available which has become an industry standard over the past 40 years.

NFPA Compliant with AccuScrub Controls

- Touchscreen controls / NEMA 3R/4/12 Enclosure / Ultrasonic water level control / Face mounted rotary disconnect / E-Stop / 24V components / Stack light with audible and visual alarms / Process interlock. Custom controls available.

COMBUSTIBLE METALS

ProVent's line of Uni-Wash Wet Dust Collectors meets or exceeds NFPA #484 for combustible metals including:

- Aluminum Dust
- **Titanium Dust**
- Magnesium Dust
- Zirconium Dust
- **Tantalum Dust**

BEYOND COMBUSTIBLE METALS

FOOD PROCESSING

ProVent has provided the food industry and others with 100% 304 Stainless Steel Wet Type Dust Collectors for the collection of a variety of airborne contaminates. If you think your application might benefit from the best designed, most efficient wet type dust collector on the market, look to ProVent and water filtration.

PHARMACEUTICAL

Utilizing water as a filtration device for pharmaceutical and biochemical dusts has it's benefits. Beyond the cost savings of not having to replace filter cartridges, employee exposure to potentially hazardous dust during this maintenance operation is relieved.



Uni-Wash—The Industry's Leading Scrub Technology

The Uni-Wash scrub technology has been continually manufactured for over 40 years. This tried and true "orifice / impingement" technology offers many benefits unmatched by other manufactures of wet type dust collection.

Utilizing airflow to produce the scrub means that there are no pumps or nozzles to clog. Additionally, this makes our wet type dust collectors more energy efficient requiring lower horsepower than other designs.

The stainless steel components of the Uni-Wash scrub are designed with a large opening that will never clog and can be cleaned effectively reducing maintenance costs. The use of the optional Sani-Ball cleaning system reduces maintenance even further.



Efficiencies of up to 95% can be reached due to the incredible turbulence created by the Uni-Wash scrub. In this turbulence, a high rate of particulate to water contact is made increasing the efficiency with a mere pressure drop of 3" wg. static pressure.


A WORD ABOUT NFPA 484


NFPA 9.4.12.6.1 "The power supply to the dustproducing equipment shall be interlocked with the airflow from the exhaust blower and the liquidlevel controller of the collector so that improper functioning of the dust-collection system will shut down the equipment it serves.."

ProVent Delivers: Both water level and motor controls are integrated into a single, custom control panel which includes a transformer and disconnect features.

The AccuScrub Control Panel options integrate airflow monitoring, audio/visual alarms, a positive vent fan and auxiliary contact into the control panel. The auxiliary contact provides the customer the ability to connect the dust producing equipment to the dust collector per NFPA guidelines

Standard Uni-Wash UC 500-3,000 CFM





Uni-Wash— Control Options

ACROSS THE LINE STARTER

The Across-The-Line provides a contactor and push buttons to start and stop the collector

COMBINATION STARTER

The Combination Control Panel provides the below enhancements to the Across-The-Line starter.

- Rotary Disconnect
- E-Stop

AccuScrub Control Panel



NFPA 484 COMPLIANT

- 7 INCH HMI TOUCHSCREEN
- DISCONNECT
- ULTRASONIC WATER LEVEL CONTROL
- E-STOP
- PROCESS INTERLOCK

- STACK LIGHT / HORN
- HIGH/LOW WATER ALARM
- LOW AIR ALARM
- 24V LOW VOLTAGE COMPONENTS
- MOTOR TEMP MONITORING

AccuScrub PRO Control Panel



NFPA 484 COMPLIANT



The AccuScrub PRO includes everything in the AccuScrub plus the additional items listed below.

- 10 INCH HMI FOR DIRECT USER INTERFACE, INPUT CONTROLS AND REAL-TIME OPERATING STATUS
- VARIABLE FREQUENCY DRIVE
- PID LOOP FOR OPTIMAL PERFORMANCE
- REAL-TIME OPERATING STATUS

Popular Options

All ProVent equipment is available in painted or unpainted stainless steel. Popular with the food processing industry, stainless steel provides cleanliness and longevity to the equipment.






The Sani-Ball cleaning system uses powerful 316 stainless steel spray nozzles to simplify and improve the cleaning process.


Ducted Systems < 4000 CFM can be raised on legs and drained from the bottom of the dust collector. This option is ideal for water soluble applications.





ProVent Silencers reduce the noise level produced by the exhausted air. ProVent manufactures silencers that are perfectly matched to the collectors they serve.







Uni-Wash UC (500 CFM—3,000 CFM) Specifications

ill-vvusil oc (5	ou ci ivi—s	DOUG CI IVI	Jopechicul	.10113	
	UC-5	UC-10	UC-20	UC-25	UC-30
Air Flow	500	1,000	2,000	2,500	3,000
Ext. SP (in. Wg)	5	4	6	5	4
Motor / Fan RPM	3450	3450	3450	3450	3450
TEFC Motor, HP	1.5	2	5	5	5
Drive Config	Direct	Direct	Direct	Direct	Direct
Primary Voltage	460Volt 3 Phase 60 Hertz				
Full Load Amps	2.6	3.4	7.6	7.6	7.6
Dry Weight (lbs)	400	650	720	850	960
Tank Capacity (US GAL)	20	42	87	97	113
Fresh Water Con- nection	3/4" NPT, Female				
Drain Connection	1 1/4" NPT, Female				
Integral Fans	AMCA Rated Injection Molded GRP Polyamide Backward Curved Airfoil Spark Resistant, Corrosion-proof, Stronger than Steel / Half the Weight / Lower HP				
Housing Con- struction	7, 10 and 12 gauge, 3/16" and 1/4" plate, Solid Welded				
Scrub Compo- nents	304 Stainless Steel, Scrub Cone, Target Plate, Adjustable Riser, Spider Support Assembly				
Internal Tank Coating	AmerLock-2 by Ameron is a 2-Part Epoxy that provides exceptional corrosion protection in harsh industrial & marine corrosive environments				
External Coating	Durethane DTM by PPG is a direct-to-metal Urethane Mastic coating that is chemically resistant and extremely durable. It provides excellent corrosion resistance and has superior color and gloss retention, excellent adhesion, UV protection. ProVent Blue standard, custom colors optionally available.				
Water Level Control	Low Maintenance mechanical float type with auto shutdown				
Motor Control Options	NEMA 12 Start/Stop Station with overload protection Combination Control Panel with E-Stop and Rotary Disconnect AccuScrub Control Panel—NFPA 484 Compliant AccuScrub PRO Control Panel—10" HMI, VFD, NFPA 484 Compliant				